# **DATA SHEET**

# TA05 SPATULA TEMPERATURE PROBE TYPE 'T'

# PALLET TEMPERATURE PROBE - Type 'T'

## Description

This probe uses the straight handle for fine control. The probe is designed for the measurement of temperature between products. Most commonly used as part of a goods inward inspection procedure. May also be used for liquid temperature measurement.

## Construction

Stainless Steel Blade 300mm Long with 7mm x 250mm Flat: Stainless Steel 316 (Food Grade) 2M curly polyurethane cable with moulded connector. Complete waterproof assembly. This provides the user with a far more robust product than the foil type of between pack probe.

### Sensor Features

TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

#### WATERPROOF HANDLE

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

### > TOUGH POLYURETHANE CABLE

- Polyurethane cables are used in place of the standard PVC for the following reasons:-
- Greater retractability
- · Enhanced memory of it's curl
- Non-Toxic
- Greater mechanical strength for durability
- 12 X 0.2mm wires used internally for greater strength.
- PTFE inner insulation for strength and retractability.

### ► HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT

Type 'T' Thermocouple : ½ Class I (±0.25°C ±0.15%)

### POLYPROPYLENE HANDLES

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

WIDE AMBIENT TEMPERATURE SPECIFICATION : -30 TO 50 °C
► TIME RESPONSE (96% of value in water) : 3.0 Secs
► MEASUREMENT RANGE : -100 TO 250 °C

### **Cross-reference for compatible instruments**

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY